




TOLERANCE = ±.010

COIL: @ 25°C

RESISTANCE 300 OHMS ± 10%

NOMINAL VOLTAGE 28.0 VDC

MUST OPERATE 13.0 VDC

MUST RELEASE 7.0 VDC MAX, 1.6 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 50 g's 11 MS. DURATION


TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE & RELEASE 10 MS MAX.

OPERATE BOUNCE 2 MS MAX.

RELEASE BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 10 AMPS 28 VDC,
10 AMPS 115 VAC 400 HZ RESISTIVE
100,000 OPERATIONS

DR. R.B. 9/14/98 CK. 9/14/98 MB

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL
CUST. NO. MS27245-3

TYPE '07' RELAY

B07D112BC4-0203