




DESCRIPTION: HIGH DENSITY FEMALE - VERTICAL DIP - LOW PROFILE - STAMPED

44 PIN SHOWN



MATERIAL:

- SHELL: STEEL, NICKEL PLATED
INSULATOR: PBT, UL 94V-O RATED, 230°C PROCESS TEMP
CHEMICAL RESISTANCE, BLACK
CONTACT: PHOSPHOR BRONZE, GOLD FLASH ENTIRE CONTACT

ELECTRICAL:

- CURRENT RATING: 2 AMPS
WITHSTANDING VOLTAGE: 1,000VAC AT SEA LEVEL
CONTACT RESISTANCE: 10 mOhms Max.
INSULATION RESISTANCE: 5,000 MOhms min.
VOLTAGE: 500VAC FOR 1 MINUTE
TEMPERATURE: -55° C TO +125° C

RoHS COMPLIANT

4 ROWS






No. OF PINS	DIMENSIONS			
	A	B	C	D
15	1.214	0.984	0.405	0.090
	30.80	24.99	10.29	2.29
26	1.545	1.312	0.765	0.090
	39.24	33.32	19.43	2.29
44	2.088	1.852	1.305	0.090
	53.04	47.04	33.15	2.29
62	2.730	2.500	1.948	0.095
	69.34	63.50	49.47	2.41
78	2.635	2.406	1.805	0.095
	66.93	61.11	45.85	2.41

195-YYY-2 1 3 L YY 1

SERIES _____
POSITIONS _____
015 _____
026 _____
044 _____
062 _____
078 _____
GENDER _____
2 = FEMALE
TERMINATION _____
1 = PC MOUNT
SHELL PLATING _____
3 = NICKEL
RoHS COMPLIANT _____
LOW PROCESS TEMP. - 230°C
HARDWARE OPTIONS _____
00 = NO HARDWARE
03 = 4-40 HEX STANDOFFS
55 = 4-40 INSERTS
PLATING OPTIONS _____
1 = GOLD FLASH

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: PAM JENKINS		DATE: 09-12-05			
			CHECKED:		DATE:			
NorComp			SCALE: 1 : 1	SHEET 1 OF 3		REV 5		
			DWG NO. 195-YYY-213L YY1					



HIGH DENSITY
VERTICAL


* TYP. ON ALL SIZES

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 03-09-06	
			CHECKED:		DATE:	
	NorComp		SCALE: FULL		SHEET 2 OF 3	
DWG NO. 195-YYY-213LYY1			REV 5			

TOLERANCE:
ALL DIMENSIONS ARE ±0.010

55X 0.158" (BOARD SIDE)



03X 0.158" (BOARD SIDE) - 0.230" MATING SIDE



DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

DATE:
12-21-09

CHECKED:

DATE:

SCALE:

SHEET 3 OF 3

REV 5

DWG NO.

195-YYY-213LYY1

RoHS COMPLIANT

NorComp