

D

D

△1 AMP LOGO AND CAVITY NUMBER LOCATED ON EITHER SURFACE.




△2 CIRCUIT NUMBER LOCATED ON EITHER SURFACE.

C

C


(OPPOSITE SIDE-OPTIONAL)

(OPPOSITE SIDE-OPTIONAL)



B


B



0.035 IN ³	BLACK	770342-3
0.035 IN ³	NATURAL	770342-1
VOLUME	COLOR	PART NUMBER

A

A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 22MAY2007	TE Connectivity		
DIMENSIONS: mm[INCHES]		CHK C. CASH 22MAY2007			
		APVD C. CASH 22MAY2007	NAME RECEPTACLE, 2 CIRCUIT, .062 PIN AND SOCKET		
		PRODUCT SPEC -	SIZE A2		
MATERIAL NYLON, UL94V-2		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APPLICATION SPEC -	CAGE CODE 00779	DRAWING NO C= 770342
		WEIGHT -	RESTRICTED TO -		
		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1
				REV H2	