

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

33467-0003

Status:

Active

Overview:

MX64 Sealed Single Row Connectors

Description:

2.54mm Pitch MX64™ Terminal, Gold (Au) Plating, 22 AWG, Right Reel Payoff, Also used with MX123™ Female Receptacle Housing



Documents:

Drawing (PDF)

Application Specification AS-33468-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	33467
Application	Power
Comments	Right Reel Payoff
Crimp Quality Equipment	Yes
Overview	MX64 Sealed Single Row Connectors
Product Name	MX123, MX64™
UPC	756054749715
Physical	
Gender	Female
Material - Metal	Copper
Material - Plating Mating	Gold
Net Weight	0.225/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50-2.06mm
Wire Size AWG	22
Wire Size mm²	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-33468-001
Sales Drawing	SD-33468-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

33467Series

Use With

MX64™ Sealed Single Row Crimp Housing 31403 , MX123™ Female Receptacle Housing 34566 , 34576

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Manual Extraction Tool	0638131400
Hand Crimp Tool	0638114200

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION