

Desktop Products

M-5400 Series PowerWheel Mouse



**PowerWheel Mouse
with Optical Sensor for
Precise Movements**

Key Features

- Optical sensor for precise movement of the mouse pointer
- PC- and MAC-compatible with USB interface
- Precise performance with 800 dpi resolution
- Easy scrolling with PowerWheel
- Elegant design, ideally suited for right-handed and left-handed users
- Connection and disconnection during operation with USB connector
- Adapter for PS/2 interface

Part Numbers

M-5400
light grey

M-5450
black

Desktop Products

M-5400 Series PowerWheel Mouse

Part Number Legend

M-5400



M-5450



Technical Data

System Requirements

USB or PS/2 Interface

Number of Buttons

3 buttons

Cable Lengths

approx. 2.0 m

Weight

ca. 135 g (without packaging)

ca. 155 g (with packaging)

Dimensions

approx. 121 x 63 x 38 mm

(without packaging)

approx. 136 x 89 x 48 mm

(with packaging)

Current Input

max. 100 mA

Connection

USB (PS/2 via adapter)

Resolution

800 dpi

Packaging Units

50 mice per master carton

1600 or 1200 mice per pallet

Storage Temperature

-20 °C to 60 °C

Operating Temperature

0 °C to 50 °C

Agency Approvals

FCC, cURus, GS, CE, GOST-R

Microsoft Windows™ XP

Delivery Volume

1 WheelMouse optical

1 Adapter for PS/2 interface

1 Printed manual

Warranty

2 years

For information on repairs or
warranty status contact:

Cherry Technical Support

Phone: 800.510.1689

E-Mail: keyboardsupport@cherrycorp.com

Contact

Call, fax or visit our
website for more information.

Last Update: 1/01/07

Cherry Electrical Products

11200 88th Avenue
Pleasant Prairie, WI 53158

Phone: 262.942.6500

Web: www.cherrycorp.com

E-Mail: sales@cherrycorp.com

Fax: 262.942.6566

The manufacturer accepts no
liability for errors or non-availability,
and reserves the right to change
specifications without prior notice.

Technical data relates to product
specifications only. Features may
differ from those described.
Only drawings combined with
product specifications shall be
deemed binding.