



Sample photo

Order symbol: ABS 100/75 HG
Product nbr: 6081302
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074024442
El. number:
Finland: 3422255
Denmark: 8212023770
Italy: 7361027
Sweden: 2535713
Norway:

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
mm:	130	80	75	Ingress Protection (EN 60529): IP 66/67
inch:	5.1	3.1	3.0	Impact Resistance (EN 62262): IK 07
Materials:				Electrical insulation: Totally insulated
Material:	ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:	RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:	Polyamide			NEMA Class: NEMA 1, 4, 4X, 6
Cover screws colour:	Grey			Certificates:
Gasket material:	TPE			
Temperatures:				Fimko
Short term:	-40 ... 80 °C			Europe EN 62208: 2003
Continuous:	-40 ... 60 °C			Gost R
Short term:	-40 ... 175 °F			
Continuous:	-40 ... 140 °F			
Accessories:				
MIV 100	Mounting plate (Galvanized steel)			
MIN 5	DIN-15 Mounting rail			
MIN 10	DIN-15 Mounting rail			
MIV 5	DIN-35 Mounting rail			
MIV 10	DIN-35 Mounting rail			
FP A 100/130	Front plate (Aluminium)			
HFP 130	Front plate hinge series (2 pcs)			
FP 22046	Wall fastening lug (4 pcs)			

