






BRIDGE RECTIFIERS

25 to 40 Amps

SINGLE PHASE PLASTIC BRIDGE RECTIFIERS (INCLUDING GLASS PASSIVATED)

REVERSE POLARITY RECTIFIER (REVERSE POLARITY RECTIFIER)									
RF Part Number	Cross Reference	Max Avg Rectified Current	Peak Inverse Voltage	Peak Fwd Surge Current @ 8.3ms Superimposed	Max Forward Voltage @ TA = 25°C @ Rated IO	Max Reverse Current @ 25°C @ Rated PIV	Package	Outline (Typical size in inches)	
		I _O (A)	PIV(V)	I _{FSM} (A)	V _{FM} (V)	I _R (A)			
GBPC25-005		25 A	50	300	1.1@12.5A	10	1000/Box		
		25 A	100	300	1.1@12.5A	10			
		25 A	200	300	1.1@12.5A	10			
		25 A	400	300	1.1@12.5A	10			
		25 A	600	300	1.1@12.5A	10			
		25 A	800	300	1.1@12.5A	10			
		25 A	1000	300	1.1@12.5A	10			
GBPC25-005W		25 A	50	300	1.1@12.5A	10	1000/Box		
		25 A	100	300	1.1@12.5A	10			
		25 A	200	300	1.1@12.5A	10			
		25 A	400	300	1.1@12.5A	10			
		25 A	600	300	1.1@12.5A	10			
		25 A	800	300	1.1@12.5A	10			
		25 A	1000	300	1.1@12.5A	10			
GBPC25-005V		25 A	50	300	1.1@12.5A	10	1000/Box		
		25 A	100	300	1.1@12.5A	10			
		25 A	200	300	1.1@12.5A	10			
		25 A	400	300	1.1@12.5A	10			
		25 A	600	300	1.1@12.5A	10			
		25 A	800	300	1.1@12.5A	10			
		25 A	1000	300	1.1@12.5A	10			
SB3505	KBPC3505	35 A	50	300	1.1@17.5A	10	1000/Box		
		35 A	100	300	1.1@17.5A	10			
		35 A	200	300	1.1@17.5A	10			
		35 A	400	300	1.1@17.5A	10			
		35 A	600	300	1.1@17.5A	10			
		35 A	800	300	1.1@17.5A	10			
		35 A	1000	300	1.1@17.5A	10			
SB3505W	KBPC3505	35 A	50	300	1.1@17.5A	10	1000/Box		
		35 A	100	300	1.1@17.5A	10			
		35 A	200	300	1.1@17.5A	10			
		35 A	400	300	1.1@17.5A	10			
		35 A	600	300	1.1@17.5A	10			