

Main

Range of product	TeSys GS 32...1250
Device short name	Auxiliary early break and signalling contact
Product or component type	Auxiliary contact
Product compatibility	GS 32...1250
Contacts type and composition	1 NO
[Ie] rated operational current	3 A at 240 V AC-15 6 A at 120 V AC-15 1.5 A at 480 V AC-15 1.8 A at 400 V AC-15 2.8 A at 24 V DC-13 0.15 A at 400 V DC-13 0.27 A at 250 V DC-13 0.55 A at 125 V DC-13 1.4 A at 48 V DC-13

Complementary

Fuse type	BS DIN NFC
Mounting location	Front Side
Product weight	0.015 kg

Auxiliary Contacts - 1 N/O

