


1.48
[37.6]


0.80
[20.3]

1.24
[31.5]

PANDUIT PART NUMBER	MAXIMUM CABLE DIA. IN [MM]	WEIGHT LBS. (g)/100PCS
LWC75-A	0.750 (19.05)	1.20 (5.40)



TEAR TAB  3/4 SCALE



TO APPLY LATCHING WIRE CLIP:
(APPLY TO A CLEAN, GREASE FREE SURFACE)

1. REMOVE PROTECTIVE LINER
2. PLACE IN DESIRED LOCATION
3. APPLY PRESSURE TO THE TOP OF LATCHING WIRE CLIP.

—ADHESIVE BACKING: PRESSURE SENSITIVE FOAM
0.04 [1.0] THICK WITH PROTECTIVE LINER TO
EXTEND BEYOND THE EDGE FORMING A TEAR TAB.

NOTES

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION, FOR PACKAGE SIZE
2. MOUNT IS DESIGNED TO SUPPORT 0.937 lbs (425g) MAX WEIGHT ON A CLEAN, SMOOTH, DRY SURFACE.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED, AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED, ARE BEYOND PANDUIT'S CONTROL.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G00239FD_PB_LWC75A_02

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

LWC75-A. LATCHING WIRE CLIP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY <u> </u>	DATE <u> </u>
--	--

MAT'L:

	SCALE
--	-------

N/A

DATE	6/18/97
------	---------

NYLON 6/6

DRAWING NO.

GB0239FD

DWG
A
SIZE

2	1-7-98	C6SM		CHANGED NOTE 3 ON APLLCATION INSTRUCTIONS	GB0239FD	2				
1	12-15-97	JAD		REVISED DIMENSIONS ADDING METRIC VALUES	GB0239FD	1				
R	06/18/97	JOS		INITIAL RELEASE	GB0239FD	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			