

## DOLPHIN FOOTSWITCH



**Dolphin Footswitch**

### Environmental Ratings:

NEMA Type 2, 4, 6 & 6P  
EN 60529 Degree of Protection IP68  
Meets IEC 60601-2-2  
Driptight - Dusttight - Watertight

### Key Benefits

The round cover allows actuation from any direction with moderate pressure. The cover and base is molded in a high impact compound and has a nonskid base pad and mounting provisions. Foot switch is wired normally open, no ground.

Size: 3-1/2" x 4-1/8" x 1"  
Weight: 9 oz.

### SPECIFICATIONS

(Special variations are available to the O.E.M. on special order on the models listed below)

### ⚠ WARNING


|                                                                                    | CATALOG<br>NUMBER | DESCRIPTION | CIRCUIT         | FORM | ELECTRICAL<br>RATINGS                                       |
|------------------------------------------------------------------------------------|-------------------|-------------|-----------------|------|-------------------------------------------------------------|
|  | D41-SN028*        | Momentary   | SPST Wired N.O. | A    | 5 A RESISTIVE 125 VAC 28 VDC<br>3 A General Purpose 125 VAC |

\*Supplied with 8 ft. 18/2 cord without plug.

**⚠ WARNING** INTENDED FOR INDOOR USE PRIMARILY TO PROVIDE A DEGREE OF PROTECTION AGAINST THE ENTRY OF WATER DURING OCCASIONAL TEMPORARY SUBMERSION AT A LIMITED DEPTH.

# Dolphin Model

NOTE: ALL DIMENSIONS ARE FOR REFERENCE ONLY.



**NEMA Type 2, 4, 6 & 6P**  
**EN 60529 Degree of Protection IP68**  
**Meets IEC 60601-2-2**

***Driptight • Dusttight • Watertight***  
***HIGH IMPACT LOW PROFILE OMNI-DIRECTIONAL DESIGN***

**Materials of Construction:**

- Actuation from any direction with moderate pressure
- The cover and base is molded in a high impact polymeric compound
- Base includes mounting provisions

**Features & Benefits:**


- Low profile to aide in elimination of fatigue
- A nonskid base pad
- Wired normally open, no ground

**Options:**

- Stainless Steel Weight Plate Available
- Custom Cable Available
- Available in RED in Production Quantities



**⚠ WARNING** INTENDED FOR INDOOR USE PRIMARILY TO PROVIDE A DEGREE OF PROTECTION AGAINST THE ENTRY OF WATER DURING OCCASIONAL TEMPORARY SUBMERSION AT A LIMITED DEPTH.



|               |                        |
|---------------|------------------------|
| Size (HxWxD): | 1.00 x 3.50 x 4.13 In. |
| Weight:       | 9.00 oz.               |

| <b>⚠ WARNING SEE PRODUCT WARNING ON PAGE 8</b>                                                              |                               |                        |             |                 |      |                                                             |
|-------------------------------------------------------------------------------------------------------------|-------------------------------|------------------------|-------------|-----------------|------|-------------------------------------------------------------|
| SPECIFICATIONS (Special variations are available to the O.E.M. on special order on the models listed below) |                               |                        |             |                 |      |                                                             |
| AGENCY APPROVALS                                                                                            | EN 60529 Degree of Protection | CATALOG NUMBER         | DESCRIPTION | CIRCUIT         | FORM | ELECTRICAL RATINGS                                          |
| cULus                                                                                                       | IP68                          | D41-SNO28 <sup>1</sup> | Momentary   | SPST Wired N.O. | A    | 5 A Resistive 125 VAC 28 VDC<br>3 A General Purpose 125 VAC |
| <sup>1</sup> Supplied with 8 ft. 18/2 cord without plug.                                                    |                               |                        |             |                 |      |                                                             |