




CONNETTORE TIPO B (CON MOLLA DI RITEGNO INTERNA)
CONNECTOR TYPE B (WITH INTERNAL SPRING)

SEZIONE A-A
(SECTION A-A)
25° COST.

VISTA DA K
(VIEW FROM K)

TIP. CAVITA' PER TERMINALI AMP JPT P/N 929939-...
OPPURE 929937-... E RELATIVI GOMMINI
AMP P/N 828904-1, 828905-1, 282536-1.
TAPPO CAVITA' P/N 828906-2
(TYP. CAV. FOR JPT CONT. P/N 929939-.. A/O 929937-.. AND REL.
SINGLE WIRE SEAL P/N 828904-1, 828905-1, 282536-1
CAVITY PLUG P/N 828906-2)

ASSE CAVITA'
(CAVITY CENTER LINE)

ASSE CONNETTORE
(CONNECTOR CENTER LINE)

COLORE COLOR	NUMERO PART. No	N (ITEM)	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)
ROSSO (RED)	282190-8				
GIALLO (YELLOW)	282190-7				
MARRONE (BROWN)	282190-6				
BLU (BLUE)	282190-5	3	///////	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)
VERDE (GREEN)	282190-4				
NATURALE (NATURAL)	282190-3	2	NATURALE (NATURAL)	GOMMA SILICONICA (SILICONE RUBBER)	GUARNIZIONE (RUBBER GASKET)
GRIGIO (GREY)	282190-2				
NERO (BLACK)	282190-1	1	///////	PA 6.6	BLOCCETTO (HOUSING)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.3
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± 2°

CUSTOMER DWG.
FOR REFERENCE ONLY
DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

METRIC

DIAM. ISOLANTE
(INS. DIA. RANGE)
1.5-3.0mm
(REDUCED INS. CABLE)

RANGO FILO
(WIRE RANGE)
0.5-2.5 mm²

MATERIAL
-

FINISH
-

9 NOV 90
DWN Ennio CINI
CHK C. TARTARI
APVD -
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -
CUSTOMER DRAWING

TE Connectivity

2 W.SPLASH PROOF CONN.ASS'Y
with SECONDARY LOCK

SIZE A3
CAGE CODE 00779
DRAWING NO C=282190
RESTRICTED TO -

SCALE NTS
SHEET 1 OF 2
REV M

