


NOTES: UNLESS OTHERWISE SPECIFIED

- 1. P/N: XRCOLOR
HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
AVAILABLE IN TEN COLORS.
CONTACT BLADE: BERYLLIUM COPPER PER QQ-C-533. GOLD PLATED PER MIL-G-45204 B TYPE 1 0.00001 [0.000254] THICK MINIMUM.
SPRING: STAINLESS STEEL TYPE 302.

- 2. P/N: W-600/COLOR
18AWG 65X36 TINNED COPPER
0.144 [3.66] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

- 3. PERFORMANCE
MAXIMUM CURRENT: 4.0 AMPS
MAXIMUM VOLTAGE: 5000 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



REVISIONS		DATE	APPROVED
LTR	DESCRIPTION		

		CONTRACT NO.		DESCRIPTION	
		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		E-Z-HOOK [®] DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
		± .XX ± .XXX ±	±	APPROVALS	DATE
				DRAWN	R.L. 10/10
				APPROVED BY	
		MATERIAL SEE NOTE.		MINI-HOOK (XR) TO LEAD ONLY	
		FINISH SEE NOTE.		SIZE CODE IDENT NO. DRAWING NO.	
				A 08505 613XR	
		NEXT ASSY USED ON		SCALE 1:1	
		APPLICATION DO NOT SCALE DRAWING		SHEET 1 OF 1	