

Model	Length m	Input Voltage VDC	Output Voltage VAC	Modes	Frequency Hz	Batteries	Operating temperature °C
KH1.5	0.1 - 1.0	6	120	Flash/Continuous	2500	LR14 x 4	- 20 to 65
KH3	0.4 - 1.0	3	110	Flash/Continuous	2000	AA x 2	- 20 to 55
KH4	0.5 - 2.5	3	105	Flash/Continuous	2000	AA x 2	- 20 to 55
KH5	0.5 - 10.0	6	100	Flash/Continuous	2000	AAA x 4	- 20 to 55
KD5	0.5 - 14.0	6	120	Flash/Continuous	2000	AAA x 4	- 20 to 55
L5	1.0 - 6.0	12	115	Continuous	2500	12V	- 20 to 55
L10	0.5 - 15.0	12	100	Flash/Continuous	1800	12V	- 20 to 55
L30	15.0 - 30.0	12	90	Flash/Continuous	1800	12V	- 20 to 55
KD15	2.0 - 20.0	12	90	Flash/Continuous	1200	12V	- 20 to 55
KD30	5.0 - 20.0	12	90	Flash/Continuous	1200	12V	- 20 to 55
KD30B	5.0 - 30.0	12	90	Flash Continuous	700	12V	-20 to 55
KH30	15 - 40	240 (PSU)/12	100	Continuous	2000	NA	- 20 to 55
KH40	20.0 - 40	12	110	Continuous	1200	12V	- 20 to 55
KH100	60.0 - 100.0	12	120	Continuous	1200	12V	- 20 to 55
KH200D	75.0 - 230.0	240 (PSU)/24	120	Continuous/Manual Fade	1200	NA	- 20 to 55
KH400	250.0 - 600.0	240 (PSU)/12	120	Continuous	1200	NA	- 20 to 55

All figures shown are Typical & are subject to change
Please ask if this list does not show the unit you require.