



608 Series

LED Panel Mount Indicators

for 8mm Mounting Hole

SPECIFICATIONS

Lock washer & nut

Part Number	Color	Voltage (VDC)	Current (mA)	Intensity TYP. (mcd)	Figure	RoHS Compliant	Panel Thickness
608-1131-110F	Red	2	15	20	1	✓	0.236 inches (6 mm)
608-1231-110F	Green	2	15	15	1	✓	
608-1331-110F	Yellow	2	15	4	1	✓	
608-3131-110F	Red	2	15	20	2	✓	
608-3231-110F	Green	2	15	15	2	✓	
608-3331-110F	Yellow	2	15	4	2	✓	

Snap-fit

Part Number	Color	Voltage (VDC)	Current (mA)	Intensity TYP. (mcd)	Figure	RoHS Compliant	Panel Thickness
608-1132-220F	Red	6	15	60	3	✓	0.197 inches (5 mm)
608-1132-230F	Red	12	15	60	3	✓	
608-1132-240F	Red	24	15	60	3	✓	
608-1232-220F	Green	6	15	110	3	✓	
608-1232-230F	Green	12	15	110	3	✓	
608-1232-240F	Green	24	15	110	3	✓	
608-1332-220F	Yellow	6	15	90	3	✓	
608-1332-230F	Yellow	12	15	90	3	✓	
608-1332-240F	Yellow	24	15	90	3	✓	
608-2132-220F	Red	6	15	60	4	✓	
608-2132-230F	Red	12	15	60	4	✓	
608-2132-240F	Red	24	15	60	4	✓	
608-2232-220F	Green	6	15	110	4	✓	
608-2232-230F	Green	12	15	110	4	✓	
608-2232-240F	Green	24	15	110	4	✓	
608-2332-220F	Yellow	6	15	90	4	✓	
608-2332-230F	Yellow	12	15	90	4	✓	
608-2332-240F	Yellow	24	15	90	4	✓	

Dialight reserves the right to make changes at any time
in order to supply the best product possible.

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com



MDEL608X001_C