



REV.	DATE	ECR NO.	DESCRIPTION
NC	01/10/11	–	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S

NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CONTACT PIN TO SOLDER

8	FERRULE	COPPER	GOLD	1
7	COVER	BRASS	GOLD	1
6	GASKET	SILICONE	RED	1
5	RETAINER RING	SUS 304	NATURAL	1
4	CONTACT PIN	BRASS	GOLD	1
3	INSULATOR	PTFE	NATURAL	1
2	HOUSING WITH BARREL	BRASS	GOLD	1
1	SHELL	BRASS	GOLD	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
 0.5 – 8mm ± 0.20 mm
 8 – 30mm ± 0.40 mm
 30 – 120mm ± 0.50 mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
 .020 – .315 ± 0.007 "
 .315 – 1.180 ± 0.015 "
 1.180 – 4.724 ± 0.020 "

DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN M.ZHANG	01/10/11
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE	
C:/CONNEX/132122.DWG	

Amphenol Connex			
PART DESCRIPTION			
SMA REVERSE R/A CRIMP PLUG (FOR RG-58C/U, 58/U, 141/U CABLE)			
PART NO.			
132122			
DWG. NO.	132122.DWG	REV.	NC
SIZE	A	SCALE	NA