

Feed-through terminal block - MBK 10 - 1402018

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.5 mm² - 10 mm², AWG 20 - 8, Width: 7.5 mm, Color: gray, Mounting type: NS 15

Key commercial data

Packing unit	1
Minimum order quantity	50
GTIN	 4 017918 020750
Custom tariff number	85369010
Country of origin	GERMANY

Technical data

General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA

Dimensions

Width	7.5 mm
Length	33 mm
Height NS 35/7.5	32.5 mm

Technical data

Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	61 A
Nominal voltage U _N	500 V
Open side panel	nein

Connection data

Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	10 mm ²
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	6 mm ²
Conductor cross section AWG/kcmil min.	20

Feed-through terminal block - MBK 10 - 1402018

Technical data

Connection data

Conductor cross section AWG/kcmil max	8
Connection method	Screw connection

Classifications

eclass

eCl@ss 4.0	27141123
eCl@ss 4.1	27141123
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

etim

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897

unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / GOST / LR / BV / NK / GOST / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

Feed-through terminal block - MBK 10 - 1402018

Approvals

CSA	
mm ² /AWG/kcmil	26-8
Nominal current I _N	55 A
Nominal voltage U _N	300 V

UL Recognized	
mm ² /AWG/kcmil	26-8
Nominal current I _N	50 A
Nominal voltage U _N	600 V

cUL Recognized	
mm ² /AWG/kcmil	26-8
Nominal current I _N	50 A
Nominal voltage U _N	600 V

GOST	
------	--

LR

BV

NK

GOST	
------	--

cULus Recognized	
------------------	--

Feed-through terminal block - MBK 10 - 1402018

Accessories

Accessories

Assembly

DIN rail - NS 15 UNPERF 2000MM - 1401695



DIN rail, material: Steel, unperforated, height 5.5 mm, width 15 mm, length: 2 m

DIN rail perforated - NS 15 PERF 2000MM - 1401682



DIN rail, material: steel galvanized and passivated with a thick layer, perforated, height 5.5 mm, width 15 mm, length: 2000 mm

End clamp - E/MBK - 1401637



End clamp, width: 6.2 mm, color: gray

Partition plate - ATP-MBK - 1413227



Partition plate, Length: 42.5 mm, Width: 2.5 mm, Height: 41 mm, Color: gray

Bridges

Insertion bridge - EB 2- BK 4 - 0801157



Insertion bridge, 2-pos., for strip terminal block, BK 4

Insertion bridge - EB 3- BK 4 - 0801144

Insertion bridge, 3-pos., for strip terminal block, BK 4

Feed-through terminal block - MBK 10 - 1402018

Accessories

Insertion bridge - EB 10- BK 4 - 0801131

Insertion bridge, 10-pos., for strip terminal block, BK 4

© Phoenix Contact 2012 - all rights reserved
<http://www.phoenixcontact.com>