




AVAILABLE BY SPECIAL ORDER ONLY



NOTES:

- 1) ALL PRIMARY DIMENSIONS IN mm,  
SECONDARY DIMENSIONS IN INCHES.

ALTERNATE UNITS FOR REFERENCE ONLY

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT



METRIC GENERAL TOLERANCES  $\pm 0.25$   
ARE PRIMARY UNLESS OTHERWISE STATED  
1 DECIMAL PLACE  $\pm$   
2 DECIMAL PLACES  $\pm$   
ANGULAR  $\pm 1^\circ$

IMPERIAL GENERAL TOLERANCES  $\pm 0.010$   
ARE FOR REFERENCE UNLESS OTHERWISE STATED  
1 DECIMAL PLACE  $\pm$   
2 DECIMAL PLACES  $\pm$   
ANGULAR  $\pm 1^\circ$

MATERIAL:  
NYLON 6/6 (RMS-174)


COLOUR:  
NATURAL

TITLE:  
DOMED HEX NUT

PART No:  
NNE-1587-MX

DRG No:  
04-120

NPR REF:



SIZE  
A4

DRN  
NJB

DATE  
19/10/04

CHKD  
I.C

DATE  
19/10/04

SCALE  
NTS

SHEET No  
1 OF 1

| PART REF    | S        | H         | A          |
|-------------|----------|-----------|------------|
| NNE-1587-M3 | 6[.237]  | 5.5[.217] | 4.5[.177]  |
| NNE-1587-M4 | 8[.315]  | 7[.276]   | 6.5[.256]  |
| NNE-1587-M5 | 10[.394] | 8[.315]   | 8.5[.335]  |
| NNE-1587-M6 | 12[.473] | 10[.394]  | 10.5[.414] |