


HSK-M-EMV-D

Metr./PG/NPT



Material
Clamping insert
Seal
O-Ring
Protection

Operating
Temperature

Nickel plated brass
Metal coated PA (Nylon)
Buna-N
Buna-N
IP 68 – 10 bar / IP 69K
within the specified clamping range

-40 °C – 100 °C (-40 °F – 212 °F)



AG	$\varnothing$ mm	GL mm	H mm	$\varnothing$ mm	Number	GL mm	Number elongated
M 12 x 1,5	3 - 6,5	6,5	25	14	1.631.1200.50	10	1.631.1200.30
M 16 x 1,5	4 - 8	6	29	17 / 19	1.631.1609.50	10	1.631.1609.30
M 16 x 1,5	5 - 10	6	32	20	1.631.1600.50	10	1.631.1600.30
M 20 x 1,5	6 - 12	6	32,5	22	1.631.2013.50	10	1.631.2013.30
M 20 x 1,5	10 - 14	6	33	24	1.631.2000.50	10	1.631.2000.30
M 25 x 1,5	13 - 18	7	39	30	1.631.2500.50	12	1.631.2500.30
M 32 x 1,5	18 - 25	8	45	40	1.631.3200.50	12	1.631.3200.30
M 40 x 1,5	24 - 32	8	51	50	1.631.4000.50	15	1.631.4000.30
M 50 x 1,5	32 - 38	9	57,5	57	1.631.5000.50		
M 63 x 1,5	37 - 44	10	52	64 / 68	1.631.6300.50		
PG 7	3 - 6,5	5	24	14	1.631.0700.01		
PG 9	4 - 8	6	28	17	1.631.0900.01		
PG 11	5 - 10	6	29	20	1.631.1100.01		
PG 13,5	6 - 12	6,5	31	22	1.631.1300.01		
PG 16	10 - 14	6,5	32	24	1.631.1600.01		
PG 21	13 - 18	7	38	30	1.631.2100.01		
PG 29	18 - 25	8	43	40	1.631.2900.01		
PG 36	24 - 32	8	48	50	1.631.3600.01		
PG 42	32 - 38	9	45	57	1.631.4200.01		
PG 48	37 - 44	10	46	64	1.631.4800.01		
3/8" NPT	4 - 8	15	29	17 / 19	1.631.3800.70		
1/2" NPT	6 - 12	13	32,5	22 / 24	1.631.1200.70		
3/4" NPT	13 - 18	13	39	30	1.631.3400.70		



Assembly instructions
see page 167

