



Clean Cut

Scissor Cut for Easy, Fray Resistant Installation in Production or Field

By adjusting the physical characteristics of the polyethylene terephthalate filaments, the engineers at Techflex have produced a product with the same specifications as our PET with the unique advantage of being able to cut the material with ordinary scissors and still maintain an extraordinarily fray-resistant end.

FLEXO CLEAN CUT (CC) is ideal for field installers and other situations where access to a hot knife is impossible. CC's fray-resistant properties allows frequent expansion at the cut end without unraveling. When cut with a hot knife, CC produces a virtually frayless end. Clean Cut sets the highest standard for uncoated fray resistance sleeving products.

- **Resists Fraying when Cut with Scissors**
- **Increased Braid Density for Fuller Coverage**
- **High Abrasion Resistance**
- **Temperature Range -94°F to 257°F**
- **Melt Temp. 482°F**



Clean Cut cuts easily and neatly with regular scissors and maintains a fray resistant end during installation.



When scissor cut, the end of Clean Cut will withstand heavier handling without fraying than standard PT.



Nominal Size	Part #	Expansion Range		Standard Spool Put-Ups		Available Colors	Lbs/100'
		Min.	Max.	Bulk Spool	Shop Spool		
1/8"	CCP0.13	1/8"	1/4"	1,000'	100'	BK & GY	0.40
1/4"	CCP0.25	5/32"	7/16"	1,000'	100'	BK & GY	0.46
3/8"	CCP0.38	3/16"	5/8"	500'	100'	BK & GY	0.74
1/2"	CCP0.50	1/4"	3/4"	500'	100'	BK & GY	0.82
3/4"	CCP0.75	5/8"	1"	250'	75'	BK & GY	1.11
1"	CCP1.00	3/4"	1 3/16"	250'	50'	BK & GY	1.24
1 1/4"	CCP1.25	1"	1 1/2"	250'	50'	BK & GY	1.56
1 1/2"	CCP1.50	1 1/4"	2"	250'	50'	BK & GY	1.85
1 3/4"	CCP1.75BK	1 1/2"	2 1/8"	200'	50'	BK	2.30
2"	CCP2.00BK	1 3/4"	2 1/2"	200'	50'	BK	2.80



ABYC