


SANYO

Cadnica




Cell Type KR-1200AAE

Specifications


Nominal Capacity		1200mAh	
Nominal Voltage		1.2V	
Charging Current	Standard	120mA	
	Fast	1800mA	
Charging Time	Standard	14 to 16Hrs.	
	Fast	about 1Hr.	
Ambient Temperature	Charge	Standard	0°C to +45°C [+32°F to 113°F]
		Fast	0°C to +45°C [+32°F to 113°F]
	Discharge	-20°C to +60°C [-4°F to 140°F]	
Storage		-30°C to +50°C [-22°F to 122°F]	
Internal Impedance (Av.) (at 50% discharge)		12.0mΩ (at 1000Hz)	
Weight		31g/1.09oz	
Dimensions(D)×(H) (with tube)		14.3 ⁰ _{-0.5} × 65.3 ⁰ ₋₁	mm
		0.56 ⁰ _{-0.02} × 2.57 ⁰ _{-0.04}	inch

Typical Characteristics


Charge




Discharge (at high rate)




Charge



Discharge (at high rate)



Discharge (at low rate)



Temperature (Charge & Discharge)

