

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 939202

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


N

REV / REDRAWN / 0720-0482-95 & 0720-0002-95

14FEB95

LO

ME



1. USE FOR AN UNSTRIPPED (SINGLE)
WIRE END ONLY

2. WIRE INSUL DIA, 3.05-3.68 [0.120-0.145]

-	-	-
-	-	-
1000	LOOSE PIECE	324486
QTY	PACKAGE TYPE	PART NO


AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F]

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [in]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:



0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [0.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL
BODY, CU PER ASTM B152
INSUL, NYLON, COLOR,
BLUE

FINISH
BODY, TIN PLATE
PER MIL-T-10727

DWN L OLMEDA 14FEB95

CHK M ELLIS 14FEB95

APVD T MICHIELUTTI 14FEB95

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

SPARE WIRE CAP, BLUE

SIZE

CAGE CODE

DRAWING NO

A3

00779

C-324486

SCALE 8:1

SHEET 1 OF 1

REV N