


482 Notch-joint multigrip pliers

▷ ISO 8976, DIN ISO 8976, NF ISO 8976.



- Undercut arcs :
- Positive engagement of notches provides high power.
- Pivot pin is not load bearing.
- Self-gripping teeth.
- 5 settings.
- Presentation :
- CPE model : Chrome finish, ergonomic grips.
- EG model : Burnished finish, red PVC grips.

	e mm	A mm	B mm	C mm	H mm	L mm	ΔΔ g
482.CPE	9,5	35	30	55	60	255	365
482.EG	9,5	35	30	55	60	255	320

482.CPE**482.EG****"Extra-wide capacity" straight-jaw pliers****481.40**

- 11 positions.
- Notch joint.
- Straight serrated jaw.
- Chrome finish, PVC grips.
- Capacity : 105 mm.

ΔΔ : 1.1 kg.


**Automatic multigrip pliers****485 Automatic multigrip pliers**

- Burnished finish. PVC grips.

485.17 : Capacity Ø 28 mm, 23 mm.

485.23 : Capacity Ø 45 mm, 38 mm.

	e mm	A mm	B mm	C mm	H mm	L mm	ΔΔ g
485.17	7	28	23	42	42	170	150
485.23	10	40	30	57	70	230	380

**Self-adjusting multigrip pliers****FAST ADJUSTMENT**

*Instant automatic setting
with one hand while
clamping.*

