





Dimensions: mm (IN)



PCB Layout



Circuit Diagram

Mechanical Specifications:

- Stop strength: 3Kg for 15 seconds
- Operating force: 160±50g (101-0266), 180±50g (101-366)
- Operating temperature: -25°~+70°C
- Storage temperature: -30°~+80°C
- Travel: .25 +.02 -.1mm

Electrical Specifications:

- Life: 100,000 cycles (101-0266), 500,000 cycles(101-0366)
- Contact resistance: 100mΩ max.
- Insulation resistance: 100MΩ min. @ 500VDC
- Dielectric Strength: 250VAC for 1 minute
- Rating: 50mA / 12VDC

Soldering Process:

- Wave soldering temperature: 260°C max. for 5 seconds
- These switches are washable. They can only be submersed after they have been soldered and returned to normal temperature.

Materials:

- Cover: stainless steel
- Contacts: silver clad phosphor bronze
- Terminals: silver clad brass
- Base: PPA, black

Tactile Switches
101-0166, 101-0266, 101-0366

Mountain
Switch

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0366](#) [101-0166](#)