

Supplier	Makita			Hitachi
Model number	HP2051	HP2010N	HP2070	DV20VB2
Input power (W)	720	750	1010	790
No load speed (rpm)	0-1200/0-2900	0-900/0-2300	0-1200/0-2900	0-1000/0-3000
Blows/min	0-24000/0-580000-18000/0-460000-24000/0-580000-13000/0-39000			
Drilling capacity steel (mm)	13	13	18	13
Drilling capacity wood (mm)	40	40	40	40
Drilling capacity concrete (mm)	20	20	20	20
Weight (kg)	2.3	3.0	2.4	2.2
Order code (230v)	138-2576 ●	138-2574 ●	138-2620 ●	866-5664
Order code (110v)	138-2577 ●	138-2575 ●	138-2621 ●	866-5672
Price each				