


SOLDER SUFFIX	CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
	Sn100%	No	No
LF3	Sn100%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

D.C. RESISTANCE (@20°C):	4-5(tie 3+4, 5+6), 0.02 ohms max. 1-8, 1.45 ohms max.
DIELECTRIC RATING:	1000VDC, 1 minute tested by applying 1250VDC for 1 second between 1-5(tie 3+4).
INDUCTANCE:	10.0uH ±10%, 10kHz, 100mVAC, 4-5(tie 3+4, 5+6), Ls.
LEAKAGE INDUCTANCE:	0.15uH max., 100kHz, 10mAAC, 4-5(tie 1+8, 3+4, 5+6), Ls.
URNS RATIO:	(1-8):(5-4) = 10:1, tie(3+4, 5+6), ±2%.
Midcom p/n 32050R-LF3 is eiSos p/n: 750032050.	

Unless otherwise specified:
Tolerances:
Angles: ±1°
Fractions: ±1/64
Decimals: ±.005[.13]

This drawing is dual dimensioned.
Dimensions in brackets are in millimeters.

DRAWING TITLE

TRANSFORMER

eiSos p/n: 750032050

REVISIONS: SEE SHEET 1

Midcom WE
www.midcom-inc.com

DRAWING NO.

32050R/-LF3

REV.

6B
4/08

SCALE ---

SHEET 2 OF 5

DWG.# 32050R/-LF3