


Panel Mount Mini-DIN Receptacle

161-381/3-E, 161-381/4-E, 161-381/5-E,
161-381/6-E, 161-381/8-E

KOBICONN

Panel Mount Mini-DIN Receptacle 161-381/3-E, 161-381/4-E, 161-381/5-E, 161-381/6-E, 161-381/8-E



Dimensions: mm (in.)

LET	Part Name	Material	Finish
1	Housing	P.B.T.	-
2	Shield	Brass	Sn
3	Contact	Phosphor Bronze	Ag
4	Nut	Steel	Uni-Chrome

SPECIFICATIONS	
Insulation Resistance:	50M Ω Min. @250 VDC
Contact Resistance:	30m Max.
Dielectric Strength:	250 VAC for one minute
Insertion Force:	4.5 Kgf Max.
Extraction Force:	0.9 - 3 Kgf
RoHS Compliant	

Date Last Revised: 01-31-11

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC- 300868

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-381/4-E](#) [161-381/6-E](#) [161-381/5-E](#) [161-381/3-E](#) [161-381-8-E](#)