

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	
OPERATING FORCE--35 OZ APPROX		CONTACT ARRANGEMENT S P D T (4X)		DO NOT SCALE PRINT	
		SILVER CONTACT RATING		GOLD CONTACT RATING	
250 VAC ----- 5 AMP					
30 VOLTS DC RATING					
INDUCTIVE -----SEA LEVEL ----- 3 AMP		1/2 AMP			
50,000 FT ----- 2.5 AMP		1/2 AMP			
RESISTIVE -----SEA LEVEL ----- 5 AMP		1 AMP			
50,000 FT ----- 5 AMP		1 AMP			
MAXIMUM INRUSH----- 24 AMP		2 AMP			
				UNLESS OTHERWISE NOTED	
				DIMENSIONS ARE IN INCHES	
				TOLERANCES ARE:	
				ONE PLACE (.0) ±.030	
				TWO PLACE (.00) ±.015	
				THREE PLACE (.000) ±.005	
				ANGLES ±	
				WEIGHT	



MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

ASSEMBLY- PUSHBUTTON SWITCH

CATALOG LISTING
4PB364-T

4PB364-T

M

DRAWING
NUMBER

2

X

ISSUE

3

REPLACES

RELEASE NO. SR-10885

CHECK

REVISIONS

A

CO18544

VDF

18 OCT 63

B

CO19800

M B F

14 JAN 65

27 MAR 63

KAC

CHECK

27 MAR 63

DAW

CHECK

27 MAR 63

DAW

CHECK

27 MAR 63

DAW

CHECK

27 MAR 63

DAW

CHECK

27 MAR 63

DAW

CHECK

27 MAR 63

DAW

CHECK

27 MAR 63

DAW

CHECK

27 MAR 63

DAW

CHECK

27 MAR 63

DAW

CHECK


27 MAR 63

DAW

CHECK

27 MAR 63

DAW



NOTE -

- 1-(3)"IISM" TYPE BASICS WITH SILVER CONTACTS AND
(1) "IISM" TYPE WITH GOLD CONTACTS
- 2-SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 3-TERMINALS ARE PLATED FOR SOLDERING
- 4 IISM TYPE BASIC SWITCH WITH 24 K SOLID GOLD CONTACTS
IS IDENTIFIED BY YELLOW SPOT ON BOTTOM OF SWITCH
- 5-UNIT WILL OPERATE SATISFACTORILY IN TEMPERATURES FROM
MINUS 85°F TO PLUS 310°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE--35 OZ APPROX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T (4)

SILVER CONTACT RATING

250 VAC ----- 5 AMP

30 VOLTS DC RATING

INDUCTIVE ----- SEA LEVEL ----- 3 AMP

50,000 FT ----- 2.5 AMP

RESISTIVE ----- SEA LEVEL ----- 5 AMP

50,000 FT ----- 5 AMP

MAXIMUM INRUSH ----- 24 AMP

GOLD CONTACT RATING

1/2 AMP

1/2 AMP

1 AMP

1 AMP

2 AMP

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT

FO-30378

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[4PB364-T](#)