

THK.200.3T

TeeBox 4 mm to 9.5mm cable max IP67 rated supplied complete with 3 pole 3 way terminal block THA.029.A1A, max rating 32A at 450V



PRODUCT SPECIFICATIONS

Minimum cable diameter (mm)	4 mm
Maximum cable diameter (mm)	9.5mm
Fixing system	Screw
Comments	Photo is representative of product
Cable entries	3
Body material	PA66 / SEBS/ TPE
Minimum temp rating °C	-40>C
Max temp rating °C	125>C
IP rating	IP67