

NEMA L18-20R
20A 36V
120/208V AC
UL Listed
2 HP



NEMA L19-20R
20A 36V
277/480V AC
UL Listed
5 HP



NEMA L20-20R
20A 36V
347/600V AC
UL Listed

Single Flush Receptacles, Back and Side Wired

Description

Black nylon face.

Catalog Numbers

HBL2440 HBL2450 HBL2460

Insulgrip Connector Bodies IP20 SUITABILITY

Description

Black and white nylon.

Catalog Numbers

HBL2443 HBL2453 HBL2463

Note: Cord clamp range .595 to .895" (15.1 to 22.7).


Insulgrip Flanged Receptacles

Description

Nylon casing, backwired.

Catalog Numbers


HBL2446 HBL2456 HBL2466




HBL2443



NEMA L18-20P
20A 36V
120/208V AC
UL Listed
2 HP



NEMA L19-20P
20A 36V
277/480V AC
UL Listed
5 HP



NEMA L20-20P
20A 36V
347/600V AC
UL Listed

Insulgrip Plugs IP20 SUITABILITY

Description

Black and white nylon.

Catalog Numbers

HBL2441 HBL2451 HBL2461

Note: Cord clamp range .595 to .895" (15.1 to 22.7).
See page B-65 for Add-A-Shroud™ kit.

Insulgrip Flanged Inlets

Description

Nylon casing, backwired.

Catalog Numbers

HBL2445 HBL2455 HBL2465

Accessories

Wall Plates

Description

Catalog Number

Stainless steel 302/304, smooth edge, single-gang.

S720

Brass, smooth edge, single-gang.

B720

Black, smooth nylon, single-gang.

P720B

Weatherproof Boots IP55* SUITABILITY

Description

Catalog Number

Seal-Tite® triple seal cover for plug when used on a cord set or when used with flush receptacles or connector body when used with flanged inlets. Black elastomer.

HBL6035

Same as above except yellow.

HBL60CM35

Seal-Tite triple seal cover for connector, when used on interconnecting cord sets. Black elastomer.

HBL6036

Same as above except yellow.

HBL60CM36


Note: See Pages B-70, B-72 and B-73 for Accessories.

HP ratings are for receptacles and plugs only and up to 480V AC only.

HP ratings are AC only.

*When installed and used properly with plug and connector body combinations.

For technical information see page B-75.



HBL2441

