





1 CIRCULAR MIL AREA RANGE: 20,800-33,100 CM
2 TIN PL 0.00381[0.000150] MIN THK PER ASTM B 545



		328142	
		PART NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM CHK MS FEHER APVD WJ VOCKROTH PRODUCT SPEC 108-30200 APPLICATION SPEC — WEIGHT .015 LB CUSTOMER DRAWING	02/28/90 19/JAN95 19/JAN95 NAME TE Connectivity TERMINAL, AMPOWER™ , WIRE SIZE: 6 AWG SIZE A2 CAGE CODE 00779 DRAWING NO C-328142 RESTRICTED TO — SCALE 4:1 SHEET 1 of 1 REV T1
DIMENSIONS: MM[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH	± - ± - ± 0.51[0.020] ± - ± - ± - ± - 2
MATERIAL ANNEALED COPPER ASTM B-152			