


Wiha SoftFinish® Handle - Standard Series


[SHOP](#)

302 95 Set 5 Pcs. Slotted & Phillips

Item No.							
	mm	mm		Size	mm		lbs.
302 95	302 05	3.0	100	311 10	1	80	1.02
	302 15	4.0	100	311 15	2	100	
	302 25	6.5	150				


[SHOP](#)

302 94 Set 6 Pcs. Slotted & Phillips

Round blade, high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component.

Item No.							
		mm	mm		Size	mm	lbs.
302 94	302 15	4.0	100	311 10	1	80	1.29
	302 25	6.5	150	311 15	2	100	
	302 27	8.0	150				
	*302 39	4.0	25				

*Stubby screwdriver with Wiha SoftFinish handle


[SHOP](#)

302 76 Set 7 Pcs. Slotted & Phillips CVM steel, hardened, hard chromed. Wiha-Chromtop tips. Handle, multi-component, cushion grip.

Item No.	Tip Size	Blade	Tip Style	lbs.
30816	1/4	4" Hex	Keystone	1.87
30825	5/16	6" Hex	Keystone	
30218	3/16"	3" Round	Cabinet	
30219	3/16"	6" Round	Cabinet	
30222	1/4"	4" Round	Cabinet	
31110	#1	3" Round	Phillips	
31115	#2	4" Round	Phillips	

[PREVIOUS](#)

[SHOP](#)

302 98 Set 8 Pcs. Slotted & Phillips

Round blade, high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component.

Item No.							
		mm	mm		Size	mm	lbs.
302 98	302 05	3.0	100	311 10	1	80	1.87
	302 15	4.0	100	311 15	2	100	
	302 20	5.5	125	311 20	3	150	
	302 25	6.5	150				
	302 30	8.0	175				


[SHOP](#)

302 97 Set 12 Pcs. Slotted & Phillips

Round blade, high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component.

Item							
No.		mm	mm		Size	mm	lbs.
302 97	302 05	3.0	100	311 05	0	60	2.48
	302 15	4.0	100	311 10	1	80	
	302 20	5.5	125	*311 40	2	25	
	302 25	6.5	150	311 15	2	100	
	*302 65	6.5	25	311 20	3	150	
	302 30	8.0	175				
	302 35	10	200				

*Stubby screwdriver with Wiha SoftFinish handle

[NEXT](#)