

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF Fiber Optic..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Current refinements (click  to remove) Search Tips

Text Search: 'F9LD2-2M30'

Your search criteria matched only one product, shown below

F9LD2-2M30



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR -326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Part Number	F9LD2-2M30
RoHS Compliancy Status	Compliant
Part Description	ST to ST singlemode duplex patch cord, 3mm jacketed cable (two ST connectors on each end) - 9/125µm.
Product Type	ST Patch Cords
Length (m)	30
Fiber Compatibility	9/125µm
Fiber Cable Size	3mm
Fiber Cable Type	Jacketed
Fiber Type	Singlemode
Cable Color	Yellow
Cable Type	Duplex
CE Compliant	No
Connector 1 Type	ST Connector
Connector 2 Type	ST Connector
End Configurations	ST to ST
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Pricing Description	ST-ST LSZH 9µm Dupl 3mm Patch Cord 30m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.