

Search Product:

Submit

[[Advanced](#)]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[HIGH - Q TOOLS & DMM'S](#) > [FUNCTION GENERATORS & COUNTERS](#) >



2.4GHz HIGH RESOLUTION FREQUENCY COUNTER

Order Code: DVM13MFC2U



Features

- ? 8-digits green LED display with annunciators
- ? two-channel operating mode memory
- ? adjustable range and gate time
- ? high-safety design as per IEC 1010, cat. II

Specifications

- ? frequency range: 0.01Hz - 2.4GHz
- ? accuracy: time base error x frequency $\pm$ 1 digit
- ? gate time: 100 msec- 10 sec
- ? input characteristics:
 - ? channel A:
 - ? frequency range:
 - ? DC couple: 0.01Hz to 100HZ
 - ? AC couple: 100Hz to 50Mhz
 - ? sensitivity: 80mVrms
 - ? impedance: 1 Mohms
 - ? max. input voltage: 30V
 - ? channel B:
 - ? frequency range: from 50Mhz to 2.4Ghz
 - ? sensitivity: 50mVrms
 - ? impedance: 50 ohms
 - ? max. input voltage: 3V
- ? power supply: 110-220VAC $\pm$ 10%
- ? max. consumption: 5W
- ? dimensions: 270 x 215 x 100mm
- ? weight: 1.6kg

Files

- ? [EN- FR- NL- ES- DE- IT](#)

Stock Info

- ? Inner carton:
- ? Outer Carton: 6
- ? EAN Barcode:
- ? Packaging: