

ASSMANN VGA Monitor connection cable, HD15/M - HD15/M

AK-310103-200-E 4016032286738



**VGA Monitor connection cable, HD15
M/M, 20.0m, 3Coax/7C, 2xferrite, be**

Offers high-quality protection against external interferences and prevents ghost images and other image faults.

For connection of a PC, for example, with a monitor or beamer /projector.

- 1 Support 1280 x 1024 pixel with 60Hz
- 1 3 x Coax for RGB and 7 x AWG28 signal wires
- 1 2 x ferrite filters
- 1 Connector 1: HD DSUB, 15-pin, plug
- 1 Connector 2: HD DSUB, 15-pin, plug
- 1 Cable type: 3Coax + 7-wire
- 1 Display Data Channel: DDC2
- 1 Hoods: molded
- 1 Shielding: Double shielding
- 1 AWG: 28
- 1 Wire material: CU
- 1 Connector surface: nickel-plated
- 1 Ferrite filter: 2 x ferrite beads
- 1 Color cable: beige
- 1 Color connector: beige
- 1 Length: 20 m
- 1 Packaging: Polybag
- 1 Assortment: VGA Cables

ASSMANN VGA Monitor connection cable, HD15/M - HD15/M

AK-310103-200-E 4016032286738

→ Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	5	9,70	38,50	31,00	22,00	26257,00
Packaging Unit Inside	1	1,94	30,00	28,00	10,00	8400,00
Packaging Unit Single	1	1,94	30,00	28,00	10,00	8400,00
Net single without Packaging	1	1,57	22,00	20,00	7,00	3080,00

