

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080184](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Watertite Wet Location 40W Fluorescent Hand Lamp with Switch, Cord Type 16/3 SJTOOW, Cord Length 15.24m (50.0')

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130108
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Overview	Wide-Area Lighting Products
Product Name	Watertite
Type	Wide Area Lamps
UPC	78678830489
Physical	
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	69.85mm (2.750")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	N/A
Length	825.50mm (32.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Fluorescent
Cord Type - Primary	16/3 SJTOOW
Lamp Type	PL-L 40/41
Lamp Wattage - Maximum	40W
Lumens	3150
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	1940SB



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130108](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION