


LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				E	REV PER 063A-0363-01	10JUL01	JR/TM



- NOTE:
- 1. STAMP AMP 4* LOCATE APPROX AS SHOWN
 - 2. TONGUE MATERIAL THK 1.22±0.08 [.048±.003]
 - 3. WIRE INSULATION DIA 13.08 [.515] MAX

AMP
WIRE RANGE

4 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150°c		DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20 [.008] 3 PLC DEC ± - ANGLES ± -		DR 10-6-93 S.S. GOULDEN		AMP AMP Incorporated Harrisburg, PA 17105-3608						
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 V MAX		CHK 10-6-93 R. HERSEY									
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 16.77-26.65mm² [33,100-52,600] STRANDED		MATERIAL COPPER PER ASTM B-152 PVF², COLOR:NATURAL		APPD 10-6-93 B. BARE		NAME TERMINAL, RING TONGUE, PVF² PLASTI-GRIP, WIRE SIZE:4 AWG					
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		FINISH TIN/LEAD (93-7) PLATE PER ASTM B545		APPD 10-6-93 M. ELLIS							
						PRODUCT SPEC NOT AVAILABLE		APPLICATION SPEC NOT AVAILABLE		SIZE B		CAGE CODE 00779		DRAWING NO C-53951	
						WEIGHT -		SCALE NTS		SHEET 1 OF 1					