



Termékek

Rólunk	
Termékek	
Újdonságok	
Cable Ties and Fixings	(1636)
Insulation Products	(2249)
Cable Protection Systems	(1667)
HelaGuard Non-Metallic Conduits and Fittings	(522)
HelaGuard Steel Conduits and Fittings	(95)
HelaGuard Steel Conduits with Plastic Coating and Fittings	(134)
HelaGuard Steel Conduits with Liquid-Tight Cover and Fittings	(82)
HelaGuard Steel Conduits with Plastic Coating and Steel Overbraid	(62)
HelaGuard Steel Conduits with Steel Overbraid and Fittings	(41)
HelaGuard PSR and PSRSC Spiral-Reinforced PVC Conduits and Fittings	(63)
HelaGuard Accessories	(210)
FlexiGuard Flexible Conduits and Fittings	(32)
Conduits for extreme conditions	(10)
Cable Management Systems	(46)
Spiral Binding	(94)
Wiring Ducts and Accessories	(8)
Wiring Ducts and Accessories 2	(8)
Braided Sleeving and Fabric Tubing	(165)
Edge Protection	(28)
Grommets	(67)
Installation Devices	(168)
Identification Systems	(2191)
Application Tooling	(129)
Connectivity	(0)
Connectivity	(0)
Kompetenciák	
Hírek & Események	
Letöltések	

Non-Metallic Conduits HG-LW16



HelaGuard PA6 Light is very flexible and can be used in moving applications.

HG-LW PA6 Light Weight, Cikkszám: 166-11203

- Light weight
- Very flexible and high fatigue life
- Small bending radius
- High impact strength and recovers if crushed
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus
- Colour: black; grey (RAL 7031) on request

Machine building, plant construction, control panels and public buildings, wherever lower mechanical protection is required.



Catalogue page (Date of issue: April 2011)



All catalogue pages



Nyomtatás

▼ Base Data	
Colour	Black (BK)
Conduit Model	Plastic corrugated
Features and Benefits 2	Light weight corrugated flexible conduit.
Pitch Type	fine
Product Family	HG-LW PA6 Light Weight
Product Group	Non-Metallic Conduits
Type	HG-LW16-PA6-BK-50M
▼ Product Dimensions	
Bending Radius	35 mm
Inside ∅	11.8 mm
Length (L)	50 m
NW ∅	12 mm
Nominal ∅	16 mm
Outside ∅ (OD)	15.8 mm
Weight (g/m)	36
∅ D	11.8 mm
▼ Logisitic and Packaging	
Carton Quantity	1250 Meter
EAN code	4031026302423
Pack Cont.	50 m
Quantity of Europallet	1250 pcs.
Quantity per	Reel
Reel Length	50 m
Weight (Kg)	3.6 kg
▼ Material and Specifications	
EN61386 Classification	24244066-110
Flammability	self-extinguishing according to EN IEC 61386
Halogenfree	YES
IP-Rating	IP66 (in conjunction with HG fittings)
Material	Polyamide 6 (PA6)
Material Shortcut	PA6
Operating Temperature	-40 °C to +120 °C
Operating Temperature Moving	-20 °C to +100 °C
Specification	UL-Recognised, IEC 61386