

tightening torque/thread 5.0 Nm/M 6 Inspection Test Pattern Size B 8

Type Cat.-No. Qty.p.pck.


SRSL 35-T35 41199.2 green/yellow 20

Ratings:

Dimensions TS 35
LxBxH (mm) 58x16x71
Stripped Length 20 mm

Max Rated Cross Section

Single Wire (solid) 2.5-50 mm²
Stranded Wire (flexible) 2.5-35 mm²
Wire Size AWG 12-2



tightening torque/thread 0.7 Nm/M 2.5 Inspection Test Pattern Size A 3

Type Cat.-No. Qty.p.pck.


SRSL 2.5-T35 DRL 41062.2 green/yellow 100

Ratings:

Dimensions TS 35
LxBxH (mm) 67x6x47
Stripped Length 10 mm

Max Rated Cross Section

Single Wire (solid) 0.2-4 mm²
Stranded Wire (flexible) 0.2-2.5 mm²
Wire Size AWG 22-14



tightening torque/thread 0.7 Nm/M 2.5 Inspection Test Pattern Size A 3

Type Cat.-No. Qty.p.pck.

SRSL 2.5-T35 DR 41060.2 green/yellow 100

Ratings:

Dimensions TS 35
LxBxH (mm) 62.5x6x47
Stripped Length 10 mm

Max Rated Cross Section

Single Wire (solid) 0.2-4 mm²
Stranded Wire (flexible) 0.2-2.5 mm²
Wire Size AWG 22-14