







TYPE 111
SAME AS TYPE 10.
EXCEPT AS SHOWN




TYPE 110
SAME AS TYPE 10.
EXCEPT AS SHOWN




TYPE 109
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 108
SAME AS TYPE 10
EXCEPT AS SHOWN




TYPE 107
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 106
SAME AS TYPE 10
EXCEPT AS SHOWN




TYPE 105
SAME AS TYPE 10
EXCEPT AS SHOWN



TYPE 104
SAME AS TYPE 10
EXCEPT AS SHOWN





TYPE 103
SAME AS TYPE 10
EXCEPT AS SHOWN




TYPE 102
SAME AS TYPE 10
EXCEPT AS SHOWN

MATERIAL RECYCLING CODE - SEE CHART—



TYPE 101



- NOTES
1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 2. SEALING CODE 3 - DESIGN WILL PASS SALT FOG AND IMMERSION
TEST AFTER CONDITIONING AS SPECIFIED IN
ESA-644 (WEATHER-PACK), ESA-710 (METRI-PACK),
ESA-650 (UNDERHOOD MICRO-PACK), C-4006
(WORLD CONNECTOR), ETC WHEN MATED TO
MATING PART OR EQUIVALENT
 3. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:

TERMINAL - 15482808 OR 15326267 (18 GA), 15423490 OR 15326266 (20/22 GA)
CABLE SEAL - 15305151 (18 GA), 15366022 (20/22 GA)
○ CAVITY PLUG - 15305171
TERMINAL POSITION ASSURANCE LOCK - 15305028
 4. WHEN PARTS ARE SHIPPED THEY MUST BE PACKED IN PLASTIC BAGS
OR SHIPPING CONTAINERS MUST BE LINED WITH PLASTIC LINERS.
BAGS OR LINERS MUST BE SEALED TO AVOID FOREIGN MATTER.
 5. FOR MATING CONFIGURATION REQUIREMENTS SEE DRAWINGS
15335900, 15336019

15439568	01	AD	108	15366040	15439567	12040756			PBT
15436719	01	AD	110	15436720	15326558	12040756	B	AND	D
15436717	01	AD	111	15436718	15326558	12040756	A	AND	C
15423593	01	AD	109	15423592	15326558	12040756	A	AND	D
15413116	02	AE	108	15366040	15336003	12040756			PBT
15410728	01	AH	107	15366040	15326558	12040756			PBT
15366027	02	AH	106	15366028	15326558	12040756	B	AND	D
15366025	02	AH	106	15366026	15326558	12040756	A	AND	C
15354716	A10	-	104	15354717	15326558	12040756			PAG-GB20 GF10
15336842	02	AH	103	15336845	15326558	12040756			PAG-GB20 GF10
15336848	A10	-	102	15336849	12040756	12040756	C		PAG-GB20 GF10
15336846	A10	-	101	15336847	15326558	12040756	B	AND	D
ASB PART NO	REV	N/P	STATUS	TYPE	CONNECTOR	PLR	SEAL	BLOCKED CAVITIES	MATERIAL RECYCL CODE



SYMBOL DEFINITION	
WITHOUT AN INSPECTION REPORT SYMBOL T REQUIRE INSPECTION. IT MAY BE ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL INSPE REQUI
	LAST USED

		MISSING
NO OF ECTIONS RED	11	
NO.	12	

G SYMBOLS	DWG ST		
	DATE	STG	F
	02MY02	R	
	21JN02	R	
7	09DE02	R	

STATUS			ZONE	
REV	N/P	CHG		
12	-	-		CLEARED 154367
13	-	-		ALL PAR 154395
14	-	-		154395 153360

REVISION HISTORY		AUTH	DR	APV/APIC
				1 2
19 - REVISION COLUMN: 15436717 AND 19 - RELEASED		224587	LOA	JAA EJA
18 - REVISED NOTE 5 1		226847	JAA	EJA
18 - RELEASED				
18 - CONNECTOR PART NUMBER WAS		234423	TLD	TLD EJA
18 - RELEASED				
18 - REVISED NOTE 3		250225	EES	EES EJA
19 - WAS TYPE 105, 15436717 - WAS 06, ALL PARTS - ADDED MATERIAL		270393	CJP	CJP LN
19 - CODE TO CHART				
18 - REVISED NOTE 3 CAVITY PLUG		281066	RWG	JAA PYP
105169				

[illegible]

DELPHI					
WAFER ELECTRIC SYSTEMS WARREN, OH					
DATE _____					
09F9E9B					
09F9E9B					
ON _____					
G OF CONCERN AND RECYCLED T PER DELPHI (1994900)					
CONN F OT 150 SLID					
A					
336850					
FRANK TO	SHEET NO	STO	REV	CLP	
OF 2	I OF	R	17	-	

ש
ש
ש
ש
ש
ש
ש

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[15354716-B](#)