



Power Cord, C19 to C20, 4.5m
Part Number: AP9887



Output	
Nominal Output Voltage	230V
Maximum Total Current Draw per Phase	16A
Output Connections	(1) IEC 320 C19
	
Input	
Input Connections	IEC-320 C20
Cord Length	4.57 meters
Number of Power Cords	1
Acceptable Input Voltage	200-240 VAC
Maximum Input Current per phase	16A

Physical

Net Weight	1.59 KG
Shipping Weight	1.82 KG
Shipping Height	572.00 mm
Shipping Width	470.00 mm
Shipping Depth	114.00 mm
Color Bl	ack

Conformance

Regulatory Approvals	VDE
Standard Warranty	2 years repair or replace

Sustainable Offer Status

PEP	Available in Documentation tab
EOLI	Available in Documentation tab