

**Part Number: 91575-1404**

Image not available

Status: Contact Molex
Series: 91575
Category: PCB Headers

Series image - Reference only

Part Detail**General**

Status	Contact Molex
Category	PCB Headers
Series	91575
Application	Power, Wire-to-Board
Product Name	N/A

Physical

Breakaway	No
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
Durability (mating cycles max)	50
Glow-Wire Compliant	No
Material - Metal	High Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Plating min - Mating	2.032µm
Plating min - Termination	2.032µm
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Through Hole

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	15A
Voltage - Maximum	250V AC

Material Info

UPC	822350241946
-----	--------------

Reference - Drawing Numbers

Packaging Specification	PK-91575-008
Product Specification	PS-91575-006
Sales Drawing	SD-91575-005

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)