

	ARM OPTIONS	CONNECTION	JOINT	MISCELLANY	ART.NR.
■ HS 20W – FLEX	250 mm	230V	Without joint		14600
			With joint		14610
		12V	Without joint		14700
				Dimmer	14700DIM
			With joint	IP65	14700IP65
					14710
		24V	Without joint	Dimmer	14710DIM
					14900
			With joint	Dimmer	14900DIM
				IP65	14900IP65
					14910
				Dimmer	14910DIM
	500 mm	230V	Without joint		14100
			With joint		14110
		12V	Without joint		14300
				Dimmer	14300DIM
			With joint	IP65	14300IP65
					14310
		24V	Without joint	Dimmer	14310DIM
					14400
			With joint	Dimmer	14400DIM
				IP65	14400IP65
					14410
				Dimmer	14410DIM
	700 mm	230V	Without joint		14120
			With joint		14130
		12V	Without joint		14320
				Dimmer	14320DIM
			With joint	IP65	14320IP65
					14330
		24V	Without joint	Dimmer	14330DIM
					14420
			With joint	Dimmer	14420DIM
				IP65	14420IP65
					14430
				Dimmer	14430DIM
■ HS 20W – SPOT	Single joint	230V			14160
		12V			14360
		24V			14460
	Double joint	230V			14163
		12V			14363
		24V			14463
■ HS 20W – AAS	Two-section	12V			14355
		24V			14455
	Three-section	12V			14353
		24V			14453
FACTORY- INSTALLED ACCESSORIES	Rectangular base (for installation in tight spaces. Fits all 12 or 24V lamps; see illustration page 18)				12917
	Panel mounting 10"				15540
	Panel mounting 20"				15550
	Panel mounting 28"				15560
	Quick connector with spiral cord 14"/59" (optional for 12V lamps with flexible arm)				14540
	Quick connector with spiral cord 14"/59" (optional for 24V lamps with flexible arm)				14545
	Switch located in the lamp head				14095
	Dust seal (silicone seal, not IP certified)				14096

Mountings and Accessories, see pages 18-19.