

North America: Danboro, PA • E-mail: info@pemnet.com • Tel: +1-215-766-8853


Europe: Galway, Ireland • E-mail: europe@pemnet.com • Tel: +353-91-751714

Asia/Pacific: Singapore • E-mail: singapore@pemnet.com • Tel: +65-6-745-0660
Shanghai, China • E-mail: china@pemnet.com • Tel: +86-21-5868-3688

Part # SMTSO-440-4ET, ReelFast® Surface Mount Nuts and Spacers/Standoffs - Type SMTSO - Unified

Type SMTSO - ReelFast® surface mount nuts and standoffs are available threaded and unthreaded.

Packaged on 330 mm recyclable reels. Tape width is 24 mm. Supplied with polyimide patch for vacuum pick up. Reels conform to EIA-481.



Specifications

Thread Size .112-40 (#4-40)

Thread Code 440

Length Code 4

L - Length ± .005 .125 in



Min. Sheet Thickness .060 in

A Max. .060 in

C Max. .161 in

E ± .005 .219 in

øH - Hole Size in Sheet + .003 - .000	.166 in
øD - Min. Solder Pad	.244 in
Parts per Reel	1000
Pitch	12 mm
For Use in Sheet Hardness¹	Not Applicable
Thread Specification	Internal, ASME B1.1, 2B
Fastener Material	Carbon Steel
Standard Finish	Electro-Plated Tin, ASTM B545, Class A with Clear Preservative Coating, Annealed
CAD Supplier	PennEngineering® (PEM®)

¹ HRB - Hardness Rockwell "B" Scale. HB - Hardness Brinell.