




REVISION RECORD		
REV	DESCRIPTION	DRFT
15	ADD DATE CODE	VICTOR 3/13/2012
16	ADD PLANARITY ON PINS	Jacky 04/08/2013

NOTES:

ELECTRICAL:

- VOLTAGE RATING : 125 VAC RMS.
- CURRENT RATING : 1.5 AMP.
- CONTACT RESISTANCE : 30 MILLIOHMS MAX.
- INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
- DIELECTRIC STRENGTH : 1000 VDC RMS 60Hz, 1MIN.

MECHANICAL:


- HOUSING MATERIAL : PA10T UL94V-0./COLOR:BLACK.
- INSERT : HIGH TEMP UL94V-0.
- CONTACT MATERIAL : PHOSPHOR BRONZE t=0.35mm.
- PLATING : GOLD PLATING OVER NICKEL ON CONTACT AREA.
: MATTE Sn PLATING FOR SOLDERING PINS.
- OPERATING LIFE : 750 CYCLES MIN.
- PCB RETENTION POST-SOLDER: 18 LBS MIN.


ENVIRONMENTAL:

- STORAGE : -40°C TO +85°C.
- OPERATION: -40°C TO +85°C.
- IR REFLOW PEAK SOLDERING TEMPERATURE:
255°C TO 265°C (5-10 SECONDS).
- RoHS COMPLIANT.

MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.

PART NUMBER:	MYLAR THICKNESS	PLATING
E5288-006-02-L	0.18mm	30u''



DETACHED LISTS	MM (INCH)		RoHS Compliant		Pulse Electronics			
	TOLERANCES EXCEPT AS NOTED		TITLE					
	MM		WITH 0.18mm MYLAR					
	.0 ± 0.25	±	TOP ENTRY SMD (15.4x14.0)					
	.00 ± 0.20	±						
	.000 ± 0.10	±						
	ANGLES ± 1°		DFTO :	Jacky	DRAWING NO.	CE5288-006-02-L	SIZE	REV
			DATE :	04/08/2013	/PART NO.	E5288-006-02-L	A3	16
	THIRD ANGLE PROJECTION		SCALE :	10:3	DO NOT SCALE DRAWING		SHEET	1 OF 1
							1	1