

WIRING DIAGRAM

OUTPUT: AP6X

SHORT-CIRCUIT AND OVERLOAD PROTECTED

LOCKNUT LN-M12

M12x1

.768 19.5

.669 17.0

.157 4.0

2.0 METER CABLE

LED

.157 [4.0]

2.166 [55.0]

2.362 [60.0]

M12x1

RELATED DOCUMENTS

1.  
2.  
3.  
4.

3RD ANGLE PROJECTION

THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.

DRFT IK

DATE 2/7/97

DSGN

SCALE 1=1.0

UNIT OF MEASUREMENT

INCH [ MILLIMETER ]

DO NOT SCALE THIS DRAWING

3000 CAMPUS DRIVE  
MINNEAPOLIS, MN 55441  
1-800-544-7769  
(763) 553-7300  
(763) 553-0708 fax  
turck.com

DESCRIPTION

BC3-M12-AP6X

IDENTIFICATION NO.

M2601000

REV

D

MATERIAL

CHROME-PLATED BRASS

FINISH

ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY

CONTACT TURCK FOR MORE INFORMATION

D UPDATE SENSOR BARREL

RDS 05/18/10 31067

REV DESCRIPTION

BY DATE ECO NO.