


1/4" Round Swage Standoff - .188 Shank Diameter


Lyn-Tron Part ID: **BR6911B-0.437-43**

Qty Available: **0**
Pricing & Availability: [Click to obtain pricing for: BR6911B-0.437-43](#)
CAD Drawings:
[View CAD Drawing](#) (Internet Explorer Only)

[Download CAD Drawing](#) (Right Click and Save Target As... to download)

[Download Autodesk Design Review© 2010](#)
Conformity Statement:
[View conformity statement: BR6911B-0.437-43](#)
General Notes

- Material: Please visit our [material specifications](#) section for additional information.
- Shank Length: Please visit our [shank lengths](#) section for additional information.
- Standard Finishes:**
 - Zinc (Clear Chromate; Plate ID - 34) on brass and steel material.
 - Iridite (Gold Plate ID - 26) on aluminum material.

Material Code	Material Description
☐ AA	Aluminum (RoHS Compliant)
☐ AL	Aluminum
☒ BR	Brass (RoHS Compliant)
☐ SS	Stainless Steel (RoHS Compliant)
☐ ST	Steel (RoHS Compliant)

Basic Part No.	Thread Size
☒ 6911	4-40
☐ 6910	6-32

Shank Code	Panel Thickness	Shank Length (0.003)
☐ A	1/32	0.075
☒ B	1/16	0.105
☐ C	3/32	0.135
☐ D	1/8	0.165

Length Code	Length Value
☐ 0.125	1/8
☐ 0.187	3/16
☐ 0.250	1/4
☐ 0.312	5/16
☐ 0.375	3/8
☒ 0.437	7/16
☐ 0.500	1/2

Applicable finishes based on material code -- BR

☐ 00	Plain - None
☐ 03	Bright Dip ? Brass
☐ 31	Cadmium Clear Chromate - QQ-P-416, CL 2