




**SL... Stack Lights**  
Complete Units

	Rated operational voltage $U_e$	Number of modules	Color Configuration	Type Article no.	Price See Price List	
<b>Complete units</b>						
Basic module with stand and 100 mm tube with filament bulb						
	Continuous light IP54	110-130 V AC	3	 red yellow green	SL-100-L-RYG/130 104266	
		230 V AC	3	 red yellow green	SL-100-L-RYG/230 205351	
		24 V AC/DC	3	 red yellow green	SL-100-L-RYG/24 205352	
	Continuous light IP54	110-130 V AC	2	 red green	SL-100-L-RG/130 104265	
		230 V AC	2	 red green	SL-100-L-RG/230 205353	
		24 V AC/DC	2	 red green	SL-100-L-RG/24 205354	
<b>Custom Assemblies</b> can be ordered using FO 315 (see page 05/045) (*) = customer designation for order. Maximum of 10 characters				SL-Combination-(*) 229655		