

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0210200391

Status:

Active - Custom

Overview:

Description:

0.50mm (.020") Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 36 Circuits, 0.152m (6.00") Length


Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable
Series	21020
Comments	Contacts on the same side, Type A
Geographic Area	Americas
Overview	Premo-Flex™
Product Name	Premo-Flex™FFC Jumper
Physical	
Cable Length	0.152m (6.00")
Circuits (Loaded)	36
Packaging Type	Bag
Pitch - Term. Interface (in)	0.020 In
Pitch - Term. Interface (mm)	0.50 mm
Temperature Range - Operating	-40°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable
Electrical	
Current - Maximum	0.5A
Voltage - Maximum	30V

Material Info



Series image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Duration at Max. 30
Process Temperature (seconds)
Max. Cycles at Max. 1
Process Temperature
Process Temperature 250 max. C

Search Parts in this Series
21020 Series

Use With
Any 0.50mm (.020") Pitch Molex FFC/FPC connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION