

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1120080002](#)
Status: **Active**
Overview: [Network Diagnostics Tools](#)
Description: NetMeter Hand Held Digital DeviceNet and Carrying Case

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	112008
Approvals	CE, CUL, CE, UL certified
Comments	NetMeter & Bag; Measures 667 Parameters, NetMeter & Bag; Measures 667 Parameters
Communication Speed	125, 250, 500 Kbaud
I/O Connector	5-pole Micro-Change (M12)
IP Rating	N/A
Material - Contact	N/A
Overview	Network Diagnostics Tools
Product Literature Order No	987650-3281
Product Name	DeviceNet, NetMeter
Type	Hand Held Digital NetMeter®
UPC	78678894652

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	Yes
Diagnostics Port	Yes
Gender	N/A
Keyway	N/A
Material - Connector Body	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	140.000/g
Orientation	N/A
Poles	N/A
Temperature Range - Operating	0°C to +40°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	7-30V DC

Material Info

Engineering Number	DN-MTR-A
--------------------	----------

Reference - Drawing Numbers

Sales Drawing	E-112008-0002-000
---------------	-------------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[112008 Series](#)