

10118940-YXX-ZZZLF

NOTE 6 & 8

POLARIZATION CODE
(OPTIONAL)
SEE NOTE 9

TOTAL NB OF POSITIONS

0 : COLOR BLACK
1 : COLOR CREAM

PART NUMBER	NBR OF POS	"A"±0.2	"B"	TOOLED
10118940-Y06LF	2x3	6.54	4.00	YES
10118940-Y08LF	2x4	8.54	6.00	YES
10118940-Y10LF	2x5	10.54	8.00	YES
10118940-Y12LF	2x6	12.54	10.00	YES
10118940-Y14LF	2x7	14.54	12.00	YES
10118940-Y16LF	2x8	16.54	14.00	YES
10118940-Y18LF	2x9	18.54	16.00	NO
10118940-Y20LF	2x10	20.54	18.00	YES
10118940-Y22LF	2x11	22.54	20.00	YES
10118940-Y24LF	2x12	24.54	22.00	YES
10118940-Y26LF	2x13	26.54	24.00	NO
10118940-Y28LF	2x14	28.54	26.00	NO
10118940-Y30LF	2x15	30.54	28.00	YES
10118940-Y32LF	2x16	32.54	30.00	NO
10118940-Y34LF	2x17	34.54	32.00	YES

DESIGN FOR 10118940-006LF
& 10118940-008LF ONLY



APPLICATION
SEE NOTE 2 & 3

CAVITY FILLED EXAMPLE
(...-B01LF)
SEE NOTE 7

SCALE 5:1

- NOTES :
- 1 - MATERIAL : PA6.6 25% GLASSFILLED, UL-94V-0
 - 2 - FOR USE WITH MINITEK CTW CONTACTS:
AWG 26-30, SERIE 77138
AWG 22-24 SERIE 10044403
 - 3 - TO BE MATED WITH MINITEK HEADERS SERIES
98414 / 98416 / 98417 / 98424 AND 10075025.
 - 4 - PRODUCT SPECIFICATIONS : GS-12-415
 - 5 - PACKAGING BULK.
 - 6 - RoHS COMPLIANT, THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO ANY SOLDER PROCESS.
 - 7 - THE TRIANGLE INDICATES THE FIRST POSITION
 - 8 - PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHERS COUNTRY REGULATIONS AS PER GS-022-008.
 - 9 - FOR POLARIZATION, NUMBER THE CAVITY NUMBER TO BE SPECIFIED.
EXAMPLE: -B01 = CAVITY 01 UNFILLED.
OMIT FROM PART NUMBER IS FEATURE NOT APPLICABLE.

FCI LOGO

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	L.MULIN	12.02.01	ANGULAR		LINEAR		0.X	±0.3	size A3	Scale 5:1	
Eng	J.COMPAGNON	12.02.01					0.XX	±0.1			
Chr	J.CO	12-02-09	0°	±2°			0.XXX	±0.05	ECN	F12-0014	
Appr	F.MO	12-02-13	Product family						Spec ref		

rev	ecn no	dr	date
A	F12-0014	LMU	12-02-13
B	F12-0097	LMU	12-08-21
C	F12-0832	JFA	12-11-26
D	F12-0840	JFA	12-12-07